




邮箱 : hooya89@hooya.hk
电话 : 0769-82310511-867

SPECIFICATIONS

MECHANICAL LIFE: 30,000 make-and-break cycles.

CONTACT RESISTANCE: 20 mΩ max. initial @ 2-4VDC
100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000 MΩ min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

OPERATING TEMPERATURE: -40°C to 85°C.

MATERIALS

CASE & BUSHING - Glass filled nylon 6/6 , retardant ,
heat stabilized (UL94V-0)

ACTUATOR - Brass, chrome plated. Internal O-ring seal. standard
for all actuators.


SWITCH SUPPORT - Brass , tin plated.

TERMINALS/CONTACT - Copper.

RoHS & Lead Free

Model No.	POS.1	POS.2	POS.3
2AS1	ON	NONE	ON
Term. Comm.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



P.C. MOUNTING

	CONTACT PLATING	TERMINAL PLATING	RATINGS
Q	Silver	Gold flash over silver	3 Amps @120 VAC or 28VDC
C	Gold over Silver	Gold over silver	1 Amps @250 VAC
R	Gold	Gold	0.4 Volt-Amps(VA) max. @20V max. (AC or DC)

东莞市弘皓电子有限公司

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例)： 3：2	TITLE 圖名	Sealed Sub - Miniature Toggle Switches			SIZE 圖紙	A4	
1	Ⓐ		變更版本	NOV-02-2007		DWG NO. 圖號	2AS1T2A1M6RES			UNIT 單位	inch mm	
2	Ⓑ		增加尺寸標註	FEB-17-2009		TOLERANCE (公差)： 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR：± 5° FILE NAME：2ASP0143	REV. 版本	E	DATE 日期	MAR - 23 - 2006	SHEET 張數	1 of 1
3	Ⓒ		增加4.50/4.80尺寸標註	MAY-05-2015			CHECKED BY 審核				DRAWN BY 製圖	ODA
4	Ⓓ		SPEC更正	JAN-17-2018								
5	Ⓔ											