





SPECIFICATIONS

Applicable Wire: AWG.#30~#24

Voltage rating: 100V DC/AC

Current rating: 2A (AWG.#24)

Withstand voltage: 500V AC/min.

Working Temp: -25°C ~ +105°C

Insulation resistance: ≥500 MΩ

Contact resistance: ≤20 mΩ

MATERIAL

PHOSPHOR BRONZE C5191-H

Tin-Plating

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
		TITLE: GH1.5 端子	
		PAR	WAFER-GH1.5-DZ
		DWN	Lucas
		CHKD	Ethan
UNLESS OTHERWISE SPECIFIED TOLERANCES		APVD	Jacob
DECIMALS:	ANGLES:	SCALE 1:1	UNIT:MM
X.:±0.20	X.':±5°		
X.X:±0.10	X.X':±3°		
X.XX:±0.05	X.XX':±1°		
CUSTOMER COPY		SIZE:A4	REV:A
		SHEET:1F1	