








规格:

1. 额 定 值: DC24V 2A
2. 接触电阻:  $\leq 30\text{m}\Omega$
3. 绝缘电阻:  $\geq 100\text{M}\Omega$
4. 耐 电 压: 500VAC
5. 插 拔 力: 3N~30N
6. 使用寿命: 5000次
7. 使用温度:  $-20^{\circ}\text{C} \sim +80^{\circ}\text{C}$



P. C. B 设计参考尺寸

|    |    |     |       |    |
|----|----|-----|-------|----|
| 3  | 芯针 | 铜   | 镀铜锡   |    |
| 2  | 弹片 | 锰钢  | 镀铜锡   |    |
| 1  | 基座 | PBT | 黑色    |    |
| 序号 | 品名 | 材质  | 电镀/颜色 | 备注 |

|                                                                                       |             |         |        |                                                                                       |                   |                                                                                       |      |
|---------------------------------------------------------------------------------------|-------------|---------|--------|---------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------------------------------|------|
|  | 深圳市虹成电子有限公司 |         | 品 名    |                                                                                       | DC座               |                                                                                       |      |
|                                                                                       |             |         | 料 号    |                                                                                       | HC-DC-013-2.0-02B |                                                                                       |      |
| 一般公差                                                                                  |             | 比 列     | 1:1    |  |                   |                                                                                       |      |
| TOLERANCE                                                                             |             | SCALE   |        |                                                                                       |                   |                                                                                       |      |
| X. ± 0.5      X°. ± 5°                                                                |             | 单 位     | MM     | 制 图                                                                                   |                   |  |      |
| .X ± 0.35      .X° ± 2°                                                               |             | UNIT    |        | DRAW                                                                                  |                   |                                                                                       | AhYe |
| .XX ± 0.25      .XX° ± 1°                                                             |             | 张 数     | 审 核    |                                                                                       | 夏操云               |                                                                                       |      |
| .XXX ± 0.15      .XXX° ± 0.5°                                                         |             | PART NO | 1 OF 1 |                                                                                       |                   |                                                                                       |      |
|                                                                                       |             | 版 本     | A      | 批 准                                                                                   |                   | 赵亮亮                                                                                   |      |
|                                                                                       |             | REV     |        | APPROVE                                                                               |                   |                                                                                       |      |

