






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

H

4.3	4.5
5.0	5.5
6.0	6.5
7.0	7.5
8.0	8.5
9.0	9.5
10.0	





电 路 图



主要技术规格:

- 额 定 值: 50mA DC12V
- 接触电阻: $\leq 50m\Omega$
- 操 作 力: $260 \pm 50gf$
- 行 程: $0.3 \pm 0.1mm$
- 绝缘电阻: $\geq 100M\Omega$
- 抗电强度: 250V 50HZ 1Min.
- 寿 命: 100,000 Cycles
- 防水等级: IP67
- 防银迁移: 60V, 85℃, 90%RH/60H



PCB. 焊接图

3	盖板	PPA	黑色	
2	簧片	不锈钢	覆银	
1	基座	PPA	黑色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	轻触开关
料 号 PART NO	HC-QC6680-TFS-E

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



>0.5~2	± 0.10
>2~5	± 0.25
>5~10	± 0.30
角度	$\pm 0.5^\circ$

单 位 UNIT	MM
张 数 PART NO	1 OF 1
版 本 REV	A

制 图 DRAW	AhYe
审 核 CHECKED	夏操云
批 准 APPROVE	赵亮亮

