




B


C


D

Insert Configuration 针芯配置	302	303	304	305	306	307	309
Pin Number(View N) 针芯排列N向							
Pin Size 接触体直径 (mm)	0.9	0.9	0.7	0.7	0.5	0.5	0.5
Withstand voltage 耐电压 (V) (AC)	1000	1000	800	800	700	700	650
Rated Current 额定电流 (A)	7.0	7.0	5.0	5.0	2.5	2.0	2.0
Insulation resistance 绝缘电阻 (MΩ)	≥5000MΩ						
R(max) 接触电阻 (mΩ)	6	6	7.5	7.5	10	10	10



建议面板开孔尺寸



GENERAL TOLERANCE (UNLESS SPECIFIED)	绘图 DWN	Y.Z 2026.05.15				
≤10 ±0.15	确认 CHK				品名 TITLE	OB系列板后安装孔型插座 4芯 黄铜镀珍珠铬,焊线式
<10~≤20 ±0.25						
<20~≤50 ±0.5	核准 APVD					
Angle ±1°						
 视 角 THIRD ANGLE	单位 UNIT	MM	版本 REV	A	品号 PART NO	C160201-00051
	尺寸 SIZE	A4	页码 SHEET	1 OF 1	型号 DRAWING NO	ZEG. 0B. 304. CLL