






HAOYU




SCHEMATIC



P.C.B LAYOUT

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867



MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	ø2.0	ø2.5
APPD.	✓	

					TOLERANCE UNLESS SPECIFIED															
					UP TO 5mm: ±0.1	ANGULAR	A0	2020.09.03	首次发行		GYW									
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD								
5	DC005 PING	BRASS	1	Ni PLATED	TITLE : DC JACK			UNIT : MM	ROHS	DWN										
4	DC005 4#FLAT PIECE 2.5	BRASS	1	Ag PLATED	MODEL : DC-005S-1-2.0-PU			SCALE: 4:1	COMPLIANT	CHK'D										
3	DC005 3#SPRING 2.5	PBS/SUS	1	Ag PLATED	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司								APPD							
2	DC005 COVER	PBT耐灼热	1	BLACK/RED/YELLOW																
1	DC005 CASE	PBT耐灼热	1	BLACK/RED/YELLOW																
NO.	PART NAME	MATERIAL	QTY	FINISHING									PRO.AGL:	 	REV :A0					