



HAOYU



SCHEMATIC



P.C.B LAYOUT

邮箱: hooya89@hooya.hk
: 0769-82310511-867

PIN	ø2.0	ø2.5
APPD.	✓	

					TOLERANCE UNLESS SPECIFIED							
6	DC005SP SOLID PIN	BRASS	1	Ni PLATED	UP TO 5mm:±0.1	ANGULAR						
5	DC005SP 4#FLAT PIECE 2.5	BRASS	1	Ag PLATED(12U")	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
4	DC005 2#CURVE PIECE 2.5	BRASS	1	Ag PLATED(12U")	TITLE : DC JACK			UNIT : MM	ROHS	DWN		
3	DC005 3#SPRING 2.5	PHOSPHOR COPPER	1	Ag PLATED(12U")	MODEL : DC-005S ϕ 2.0-PU-SP(UL)			SCALE: 4:1	COMPLIANT	CHK'D		
2	DC005 COVER	PBT	1	BLACK/RED/YELLOW	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司			APPD				
1	DC005 CASE	PBT	1	BLACK/RED/YELLOW								
NO.	PART NAME	MATERIAL	QTY	FINISHING						PRO.AGL:		REV :A0

ECBT2.E509849 - Connectors for Use in Data, Signal, Control and Power Applications - Component

Connectors for Use in Data, Signal, Control and Power Applications - Component

See General Information for **Connectors** for Use in Data, Signal, Control and Power Applications - Component

YAT SHUN ELECTRONIC CO LTD

E509849

Rm 609, 6th Fl
Kwong Sang Hong Centre
151-153 Hoi Bun Rd
Kwun Tong, HONG KONG
Model(s) DC-005, DJ-220, RT-C30

Marking: Company name and model designation on the device or carton.



Last Updated on 2020-05-11

并不是所有出现在本数据库中的公司名称和产品都满足了UL 跟踪检验服务的要求。只有带有 UL 标志的产品，才应该被视为经过UL认证，并满足UL 跟踪检验服务的要求。注意查看产品上的标志。

UL 允许在线认证目录中所含材料的复制遵循以下条件：1.指南信息、装配、构造、设计、系统和/或认证（文件）必须在不篡改任何数据（或图纸）的情况下完整且无误导性地呈现。2.“经 UL 允许从在线认证目录转载”声明必须出现在所摘取材料的邻近位置。此外，转载材料必须包含以下格式的版权声明：“© 2020 UL LLC”

邮箱：hooya89@hooya.hk
电话：0769-82310511-867
v: hooya89

HOYA ELECTRONICS 浩宇电子