




HAOYU



PIN	$\phi 2.0$	$\phi 2.5$
APPD.	✓	

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867



P.C.B LAYOUT

					TOLERANCE UNLESS SPECIFIED							
					<1.5: $\pm 0.1mm$ >1.5~5.0: $\pm 0.25mm$ >5.0: $\pm 0.3mm$	ANGULAR $\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
6	DC005SP PING	BRASS	1	Ni PLATED	TITLE:DC JACK		UNIT : MM		ROHS	DWN		
5	DC005SP 4#FLAT PIECE	BRASS	1	Ag PLATED	MODEL: DC-005Q-2.0-SU-B-SP(UL)		SCALE: 5:1		COMPLIANT	CHK'D		
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司		APPD		PRO.AGL: 		REV: A0	
3	DC005Q 3#SPRING	SUS	1	Ag PLATED								
2	DC005 COVER	PA66	1	YELLOW/BLACK/RED								
1	DC005 CASE	PA66	1	YELLOW/BLACK/RED								
NO.	PART NAME	MATERIAL	QTY	FINISHING								

Connectors for Use in Data, Signal, Control and Power Applications - Component

E509849

Marking: Company name and model designation on the device or carton.

Last Updated on 2020-05-11

UL 允许在线认证目录中所含材料的复制遵循以下条件：1.指南信息、装配、构造、设计、系统和/或认证（文件）必须在不篡改任何数据（或图纸）的情况下完整且无误导性地呈现。2.“经 UL 允许从在线认证目录转载”声明必须出现在所摘取材料的邻近位置。此外，转载材料必须包含以下格式的版权声明：“© 2020 UL LLC”