








标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



MATE PLUG



ELECTRICAL CIRCUIT



RECOMMENDED PCB LAYOUT
TOP VIEW(TOLERANCE: ±0.05)

SPECIFICATIONS:



1. ELECTRICAL CHARACTERISTICS
 - 1-1.RATING: 24V 3A
 - 1-2.CONTACT RESISTANCE: 30mΩ MAX.(INITIAL)
 - 1-3.DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR ONE MINUTE
 - 1-4.INSULATION RESISTANCE:100M MIN. MEASURED BY 500V DC
2. MECHANICAL CHARACTERISTICS:
 - 2-1.INSERTION FORCE : 0.3~3.0 KGF
 - 2-2.WITHDRAWAL FORCE : 0.3~3.0 KGF
3. LIFE TEST: 5,000 CYCLES MIN.
4. FOR REFLOW SOLDERING LEAD-FREE PROCESS,

3	外壳	铜	— —	
2	芯针	铜	镀金	
1	基座	PA9T	黑色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	DC座
料 号 PART NO	HC-DC-0045T-1.3-03A

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X. ±0.5	X. ±2°	单 位 UNIT	MM	制 图 DRAW	AhYe	
X.X ±0.3	X.X ±1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
X.XX ±0.2		版 本 REV	A	批 准 APPROVE	赵亮亮	
X.XXX ±0.1						