





Mechanical
Insertion forces ≤ 20 N
Pull out the force ≤ 20 N
Service life: > 1000 pluggings
Panel thickness: Max. 3mm 0.13
Wiring: vertical PCB installation
Looking device: Latch Lock
Installation direction: rear installation
Base Shape: A
Mounting: A-Block

Material
Plating of contacts: 0.2 um Au over Ni plating
Contact: Invario (CuNi)
Inner cover: LCP 15% GR
The shell: PM6 15% GR

Environmental
Flammability: UL 94 V-0
Solderability: comply with IEC 69-2-20
Operating temperature: -30°C to 80°C



Frontplattenausschnitt (Rueckseite)
Panel cut out (rear side)

序号	名称	材料	数量	镀层/颜色	备注
7	拔柄	不锈钢	1	NI	
6	垫片	铝制	1	NI	
5	内垫片	H62	1	NI	
4	持针	PHOSPHOR BRONZE	8	10 μ	
3	后盖	LCP	1	BLACK	
2	面板	铸合金	1	镍	
1	塑座	PA66	1	BLACK	

PCB LAYOUT

网络插座外形图

绘图:	吴昊飞	日期:	2022.6.6	一般公差	品名:	RCH-KN7-198带锁 90° 圆形金属面板无基片		
审核:	周清海	日期:		30~ 10~30 ±0.25 ±0.20	料号:	KN719890-60003510035 (K161305)		
核准:	朱生文	日期:		~10 ±0.15 ±0.12	型号:	RJ45	图号:	
				角度: 1 of 1	版本:	单位:mm	比例: 1:1	纸型: A4

 温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD