



RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATE

电气特性:Electrical:

1. 额定电流: Current Rating
5A/contact terminal
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectric Withstanding Voitage:
500 V AC AT Sea Level
5. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN



原材料:Material:

1. 塑胶:Housing:pbt
2. 端子>Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC

电镀:Finish:

1. 端子Contact:Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.
3. Temperature Range:-55° C to +105° C

铆钉型式说明



DIM \ PIN	DP9S	DP15S	DP25S	DP37S
A	30.80	39.20	53.05	69.40
B	25.00	33.30	47.05	63.50
C	16.35	24.70	38.40	54.80
D	19.20	27.70	41.10	57.30
E	10.80	10.70	10.70	10.80

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	$\pm$ 0.35	X'.	$\pm$ 5'
.X	$\pm$ 0.30	.X'	$\pm$ 2'
.XX	$\pm$ 0.25	.XX'	$\pm$ 1'
.XXX	$\pm$ 0.10	.XXX'	$\pm$ 0.5'

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	920-H0108021Y00105
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	DB-180度9PIN母头铁壳PBT黑胶
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	
				版本 VER	A0