

RoHS

HF

REV.

ECN.#

DESCRIPTION

NAME








DATE

A0

NEW RELEASE

liuhongping

2023.01.02






MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd			
X' ±2'	X' ±2'	TITLE	TYPE C 24PIN 防水 沉板.12 CH0.36 端子SMT 四脚插板 露舌片	DR	
.X ±0.30	.X ±0.012	PART NO.	1043111012	CHKD	
.XX ±0.20	.XX ±0.008	PRO J.	PAGE 1/3	UNITS mm	APPD
.XXX ±0.10	.XXX ±0.004	SIZE	A4	SCALE 1:1	DIS NO.
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					

RoHS

- 备注:
1. 材质: 硅胶
 2. 电镀: 清洗

防水圈






备注:

1. 材质:
 - 1.1 塑胶: LCP UL94V-0; 颜色: 黑色
 - 1.2 端子: C7025
 - 1.3 外壳: SUS304
 - 1.4 中夹片: SUS301
2. 电镀:
 - 2.1 端子: 接触区镀金1U"; 焊接区镀金G/F; 整体镀镍30U"MIN
 - 2.2 外壳: 镀镍30U"MIN
 - 2.3 中夹片: 镀镍30U"MIN
3. 电气性能:
 - 3.1 额定电流:VBUS / GND 5A;其他接触端子 0.25A
 - 3.2 接触阻抗: 40mΩ MAX. 测试后 50mΩ MAX
 - 3.3 绝缘阻抗: 100MΩ MIN
 - 3.4 耐压: 100V AC R. M. S
4. 机械性能:
 - 4.1 插入力: 5-20N
拔出力:8-20N 测试后6-20N
 - 4.2 寿命: 10000次.
5. 环境性能:
 - 5.1 工作温度: 温度-40° C~+85° C; 湿度 80% R. H MAX
 - 5.2 盐雾: 24H
6. 焊锡:245±5° C, 5±0.5s
7. IR 炉: 220℃的回流焊60S Min, 且保持260+0/-5℃ 10S Min
(回流焊次数: 1次)

Pin	Name	Pin	Name
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND


MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd			
X.* ±2*	X.* ±2*				
.X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		TITLE	TYPE C 24PIN 防水 沉板1.12 CH0.36 端子SMT 四脚插板 露舌片	DR	
		PART NO.	1043111012	CHKD	
		PRO J.	PAGE 2/3 UNITS mm	APPD	
		SIZE	A4 SCALE 1:1 DIS NO.		

RoHS




备注

1. 卷装数量: 1500PCS/REEL
2. 载带总长度



3. 每箱包装数量: 15000PCS/CARTON



MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co., Ltd			
X.* ±2"	X.* ±2"				
.X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd		TITLE	TYPE C 24PIN 防水 沉板 1.12 CH0.36 端子 SMT 四脚插板 露舌片	DR	
		PART NO.	1043111012	CHKD	
		PRO J.	PAGE 3/3	UNITS mm	APPD
		SIZE	A4	SCALE 1:1	DIS NO.