



RoHS




目錄
MAPX

設 變 內 容
MODIFICATION

日 期
DATE



FRONT EDGE OF CONNECTOR
PCB LAYOUT (T=1.60mm)



电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Level
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:0.7kgf(MIN)
2. 端子保持力: Terminal Retenion
1.0kgf(MIN)
3. 寿命: 1500次

原材料:Matorial:

1. 塑胶:Housing:lcp
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC/c2680

电镀:Finish:

1. 端子Contact:Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.
3. Temperature Range:-55° C to +85° C

Pin NUMBER	SIGNAL NAME
1	V/BUS
2	D-
3	D+
4	GND

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	911-122B2026S10100
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	AF10.0D款前两脚无边方弹 铜壳反向LCP黑胶6.2SMT
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	 版本 VER