

RoHS

REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

HuHaoteng

2023.01.02

备注:

1. 材质:

1.1 塑胶: LCP UL94V-0; 颜色: 黑色

1.2 胶套: PA10T; 颜色: 黑色

1.3 端子: C7025

1.4 外壳: SUS304

1.5 中夹片: SUS301

1.6 吸取盖: LCP UL94V-0; 颜色: 黑色

2. 电镀:

2.1 端子: 接触区镀金1U"MIN. 焊接区镀金G/F; 整体镀镍30U"MIN

2.2 外壳: 镀镍30U"MIN

3. 电气性能:

3.1 额定电流:VBUS and GND pin 3A; 其他接触端子 0.25A

3.2 接触阻抗: 40mΩ MAX. 测试后 50mΩ MAX

3.3 绝缘阻抗: 100MΩ MIN

3.4 耐压: 100V AC R. M. S

4. 机械性能:

4.1 插入力: 5-20N

拔出力:8-20N 测试后6-20N

4.2 寿命: 10000次.








5. 环境性能:

5.1 工作温度: 温度-40° C~+85° C; 湿度 80% R.H MAX


5.2 盐雾: 24H

6. 焊锡:245±5° C, 5±0.5s

7. IR 炉: 220℃的回流焊60S Min, 且保持260+0/-5℃ 10S Min




吸取盖示意图



MILLIMETERS	INCH
X.* ±2*	X.* ±2*
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	

		东莞市金比莱五金塑胶科技有限公司			
		DONGGUAN JBL TECH CO., LTD			
TITLE		直立式防水TYPE C 24Pin SMT H8.8mm 不需防水圈		DR	
PART NO.		104317992-B		CHKD	
PRO J.		PAGE	1/2	UNITS	mm
		SIZE	A4	SCALE	1:1
		DIS NO.			


RoHS

COVER TAPE PEELING ANGLE: $165^\circ \sim 180^\circ$ PEELING FORCE: $20 \sim 130g$

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 5000PCS/CARTON

CARTON
350x350x330 K=K

MILLIMETERS	INCH
X.* $\pm 2^\circ$	X.* $\pm 2^\circ$
X ± 0.30	.X ± 0.012
XX ± 0.20	.XX ± 0.008
XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	直立式防水TYPE C 24Pin SMT H8.8mm 不带防水圈		DR		
PART NO.	104317992-B		CHKD		
PRO J.	PAGE	2/2	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.	