




- NOTES:
备注
- 1.Brass or purple copper,Bright tin-plating
黄铜或紫铜, 镀亮锡
 - 2.Wire screw hole M5
压线螺孔M5
 - 3.Current Rating: 60A
额定电流:60A
 - 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC - * ** * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	WOP	Product No.	Material
HC=Full Teeth (插牙) R=Vivet Nut (铆螺母) R=Vivet Gasket (铆垫片)	0.5~1.0mm 1.0~1.2mm 1.2~1.5mm 1.5~1.8mm 2.0~2.5mm 2.5~3.0mm 3.0~3.5mm	2~6 (螺牙) 2~6 (螺牙) 2~6 (螺牙) 2~6 (螺牙) 2~6 (螺牙) 2~6 (螺牙) 2~6 (螺牙)	2~6 (焊脚) 2~6 (焊脚) 2~6 (焊脚) 2~6 (焊脚) 2~6 (焊脚) 2~6 (焊脚) 2~6 (焊脚)	08080808mm 1620=16x20mm	WOP =WOP =WOP =WOP =WOP =WOP =WOP		默认=铜 (黄铜) =铜 (紫铜)

			GENEAL TOLERANCE	制 图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核				
			5 or more ±0.35	批 准		产品名称	PCB 焊接端子 厚度1.0 插板 铆垫片	版 本
			2~5 ±0.25	APPROVAL		TITLE	M5 4焊脚 13x12x12mm	REV.
			0~2 ±0.15	比 例		产品料号	HC-RG1054-1312-D327-07	单 位
			Angle ±3.0°	SCALE		PART NO.		UNIT
序号	变更内容	日期		投 影		材 料		页 次
No.	MODIFY CONTENT	MODIFY DATE		Projection		MATERIAL		SHEET