

REV.	MODIFICATION	ECN No.	NAME	DATE
A0	NEW			

NOTE:

1. 材质

1.1. 塑胶: PBT白色

1.2. 端子: C2680R-H T=0.25±0.01

1.3. 外壳: C2680R-H T=0.30±0.01

1.4. 中夹片: C2680R-H T=0.30±0.01

2. 机械性能:

插拔力: 插入力 35N MAX ,





拔出力 10N MIN

机械寿命: 插拔1500次

3. 端子:

打镍底50~80u", 焊脚镀锡80~120u",
接触区镀金1u"

4. 外壳: 镀镍

5. 标示"XX"为FAI检验尺寸,
标示"△"为IPQC重点检测尺寸
标示"S△"为CPK管控尺寸

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

.X: ±0.35	.X°: ±5.0°	INTENDED USE:	TITLE:
.XX: ±0.25	.XX°: ±3.0°	CUSTOMER DRAWING (客户图)	USB AF 双层180度无脚无边
.XXX: ±0.20	.XXX°: ±1.5°	APPD.:	PART NO.:
MAT'L.:		CHKD.:	DWG. NO.:
SEE NOTES		DR.:	SCALE: 1:1
			PAGE: 1/1
			UNIT: mm
			REV.: A0