



NOTES:

1. MATERIAL:

- 1). HOUSING MATERIAL: THERMOPLASTIC UL94V-0; COLOR: BLACK
- 2). CONTACT MATERIAL: BRASS, $T=0.60\text{mm}$

2. FINISH:

- 1). CONTACT FINISH: $50\mu\text{min}$ NICKEL UNDER PLATED, PLATED $3\mu\text{in}$ AU ON CONTACT AREA; PLATED COLD FLASH ON SOLDER AREA.
- 2). FIN DND FINISH: $50\mu\text{in}$ MIN. NICKEL UNDER PLATED, TIN-PLATED HIGH-TEMPER ATURR $100\sim 160\mu\text{in}$ IN THE WHOLE SURFACE.

3. ELECTRICAL SPECIFICATIONS:

- 1). VOLTAGE RATING: 12 VAC
- 2). CURRENT RATING: 2.0A
- 3). DIELECTRIC STRENGTH: 250V AC FOR MINUTE
- 4). INSULATION RESISTANCE: 500 M Ω
- 5). CONTACT RESISTANCE: 50M Ω
- 6). OPERATION TEMPERATURE: -40°C TO $+105^{\circ}\text{C}$
- 7). MAX. PROCESSING TEMP: 260°C FOR 30 SECONDS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.7PH 4.5H 3PIN 刀式电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW02-BC3P3745	
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606171445	
			SHEET NO. 1 OF 1	