







PCB Layout

UL Standard

- 1.Rating voltage/current: 300V/15A
2.withstanding voltage: AC2000V/1Min

IEC Standard

1. Pollution Degree	2
Overvoltage Category	III
Rate Impulse Voltage(KV)	4.0KV
Rate Voltage(V)	320V
Rate Current(A)	15A

NOTES2:

- 1.Housing: PA66 (UL94V-0)
2.Solder Pin: Brass (Sn Plated)

NOTES3:

- 1.Pitch: 5.08mm Poles: 02-24P
2.Operating temperature: -40℃~+105℃
3.RoHS Compliance

How to order

MX2EDGVC - 5.08 - XXP - XXXX - XX - X

产品型号 间距 极数

颜色: 01:常规颜色
02-99:定制颜色

灰色:GY 橙色:OE
蓝色:BU 红色:RD
黑色:BK 透明色:TT
绿色:GN 黄色:YW
白色:WE

Cu:铜
Fe:铁

A-Z其他定制

Pitch Range In mm			Nominal Dimension Range In mm					—		
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
										
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL		NOTE	
DWG.	CKK	DATE	22.09.14	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE			MX2EDGVC-5.08-XXP			
 CIXI MAIXU ELECTRONICS CO., LTD. 慈溪市迈旭电子有限公司				NAME				
				DWGNO.				