



技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 150V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材质:

1. 塑胶: PA66 白色

型号	CKT	A	B	C
ZX-DF1.25-2-5PJK	2*5	10.50	5.00	7.86
ZX-DF1.25-2-6PJK	2*6	11.75	6.25	9.11
ZX-DF1.25-2-7PJK	2*7	13.00	7.50	10.36
ZX-DF1.25-2-8PJK	2*8	14.25	8.75	11.61
ZX-DF1.25-2-9PJK	2*9	15.50	10.00	12.86
ZX-DF1.25-2-10PJK	2*10	16.75	11.25	14.11
ZX-DF1.25-2-11PJK	2*11	18.00	12.50	15.36
ZX-DF1.25-2-12PJK	2*12	19.25	13.75	16.61
ZX-DF1.25-2-14PJK	2*14	21.75	16.25	19.11
ZX-DF1.25-2-15PJK	2*15	23.00	17.50	20.36
ZX-DF1.25-2-16PJK	2*16	24.25	18.75	21.61
ZX-DF1.25-2-17PJK	2*17	25.50	20.00	22.86
ZX-DF1.25-2-18PJK	2*18	26.75	21.25	24.11
ZX-DF1.25-2-19PJK	2*19	28.00	22.50	25.36
ZX-DF1.25-2-20PJK	2*20	29.25	23.75	26.61
ZX-DF1.25-2-21PJK	2*21	30.50	25.00	27.86
ZX-DF1.25-2-22PJK	2*22	31.75	26.25	29.11
ZX-DF1.25-2-23PJK	2*23	33.00	27.50	30.36
ZX-DF1.25-2-24PJK	2*24	34.25	28.75	31.61
ZX-DF1.25-2-25PJK	2*25	35.50	30.00	32.86



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE		料号 PART NO.	ZX-DF1.25-2-NPJK	版本 REV.	A
			.X	± 0.30	X.*	$\pm 5^{\circ}$	审核 CHECK	品名 TITLE	1.25 Pitch A型(DF13)双排公头胶壳	页次 SHEET	1/1
			.XX	± 0.25	X.X*	$\pm 1^{\circ}$	核准 APPROVAL	客户料号 CUTM.NO.			
			.XXX	± 0.15			单位 UNITS	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	
							MM				