







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值).
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC
(使用AWG#32, $0.038 \pm 0.02\text{mm}$).
7. 耐电压: AC 200V/1分钟.



Part No	CKT	A	B	C	D
BX-0.8-2PJK-XM3	2	0.80	1.78	2.18	2.40
BX-0.8-3PJK-XM3	3	1.60	2.58	2.98	3.20
BX-0.8-4PJK-XM3	4	2.40	3.38	3.78	4.00
BX-0.8-5PJK-XM3	5	3.20	4.18	4.58	4.80
BX-0.8-6PJK-XM3	6	4.00	4.98	5.38	5.60
BX-0.8-7PJK-XM3	7	4.80	5.78	6.18	6.40
BX-0.8-8PJK-XM3	8	5.60	6.58	6.98	7.20
BX-0.8-9PJK-XM3	9	6.40	7.38	7.78	8.00
BX-0.8-10PJK-XM3	10	7.20	8.18	8.58	8.80
BX-0.8-11PJK-XM3	11	8.00	8.98	9.38	9.60
BX-0.8-12PJK-XM3	12	8.80	9.78	10.18	10.40
BX-0.8-13PJK-XM3	13	9.60	10.58	10.98	11.20
BX-0.8-14PJK-XM3	14	10.40	11.38	11.78	12.00
BX-0.8-15PJK-XM3	15	11.20	12.18	12.58	12.80
BX-0.8-16PJK-XM3	16	12.00	12.98	13.38	13.60
BX-0.8-17PJK-XM3	17	12.80	13.78	14.18	14.40
BX-0.8-18PJK-XM3	18	13.60	14.58	14.98	15.20
BX-0.8-19PJK-XM3	19	14.40	15.38	15.78	16.00
BX-0.8-20PJK-XM3	20	15.20	16.18	16.58	16.80

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-0.8-NPJK-XM3	版本 REV.	A
1	0.8-C型WTB刺破型公头胶芯	PA66加玻纤 UL94 V-0 米黄色				X. ± 0.5 $\pm 1^{\circ}$	审核 CHECK	EVA	品名 TITLE	0.80 Pitch C型WTB刺破公头	页次 SHEET	1/1
2	0.8-C型WTB刺破型公头端子	铜合金/镀金				X.X ± 0.2	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
						X.XX ± 0.1	单位 UNITS	MM	比例 SCALE	1:1		

Bossie (博锡)