








技术指标(Technical Index):

1. 工作温度(Temperature range): $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 30V AC/DC .
3. 额定电流(Rated current): 0.5A AC/DC .
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Dielectricwithstanding voltage): 200V AC/minute .
6. 绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
7. 适用线规(Apply to gauge): AWG#28~#32(O.D0.6mm MAX).

序号	品名	材质	制图	变更内容	日期	GENERAL TOLERANCE		制图	ROSE			料号	ZX-0.8-DZ-XM2		版本	A	
			DRAWN	DESCRIPTION	DATE			DRAWING				PART NO.					
						X.	±0.5	±1°	审核	LEO			品名	0.80 Pitch C型WTB公头端子		页次	1/1
						X.X	±0.2		CHECK				客户料号				
1	端子	Phosphor Bronze Bright tin plated				X.XX	±0.1	核准	JOHN			CUTM.NO.					
								单位	MM	比例	1:1	兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.					
								UNITS		SCALE							