

PCB LAYOUT TOLERANCE: ±0.05

NOTES:

1. MATERIAL:

1). HOUSING MATERIAL: THERMOPLASTIC UL94V-0; COLOR: BLACK

2). CONTACT MATERIAL: BRASS, T=0.60mm

2. FINISH:

1). CONTACT FINISH: 50" MIN. NICKEL UNDER PLATED, PLATED 3u" AU ON CONTACT AREA; PLATED COLD FLASH ON SOLDER AREA.

2). FINISH: 50u" MIN. NICKEL UNDER PLATED, TIN-PLATED HIGH-TEMPERATURE 100~160u" IN THE WHOLE SURFACE.

3. ELECTRICAL SPECIFICATIONS:

1). VOLTAGE RATING: 12 VAC

2). CURRENT RATING: 2.0A

3). DIELECTRIC STRENGTH: 250V AC FOR MINUTE

4). INSULATION RESISTANCE: 500 MΩ

5). CONTACT RESISTANCE: 50MΩ

6). OPERATION TEMPERATURE: -40° C TO +105° C

7). MAX. PROCESSING TEMP: 260° C FOR 30 SECONDS



深圳市华宇创精密电子有限公司


TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2" X.X' ±0.5"



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

3.7PH 4.3H 3PIN 刀式电池座

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW-BC3P3743

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2606171457

SHEET NO.

1 OF 1