






技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

材料

1. 塑胶: PA66 白色

型号	CKT	A	B	C
ZX-PHB2.0-2-2PJK	2*2	2.00	7.00	2.90
ZX-PHB2.0-2-3PJK	2*3	4.00	9.00	3.10
ZX-PHB2.0-2-4PJK	2*4	6.00	11.00	4.30
ZX-PHB2.0-2-5PJK	2*5	8.00	13.00	6.30
ZX-PHB2.0-2-6PJK	2*6	10.00	15.00	8.30
ZX-PHB2.0-2-7PJK	2*7	12.00	17.00	6.30
ZX-PHB2.0-2-8PJK	2*8	14.00	19.00	8.30
ZX-PHB2.0-2-9PJK	2*9	16.00	21.00	14.30
ZX-PHB2.0-2-10PJK	2*10	18.00	23.00	14.30
ZX-PHB2.0-2-11PJK	2*11	20.00	25.00	14.30
ZX-PHB2.0-2-12PJK	2*12	22.00	27.00	14.30
ZX-PHB2.0-2-13PJK	2*13	24.00	29.00	14.30
ZX-PHB2.0-2-14PJK	2*14	26.00	31.00	14.30
ZX-PHB2.0-2-15PJK	2*15	28.00	33.00	14.30
ZX-PHB2.0-2-16PJK	2*16	30.00	35.00	14.30
ZX-PHB2.0-2-22PJK	2*22	42.00	47.00	14.30

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-PHB2.0-2-NPJK	版本 REV.	A		
			.X	±0.30	X.*	±5°	审核 CHECK	LEO			品名 TITLE	PHB2.0公头胶壳	页次 SHEET	1/1
			.XX	±0.25	X.X*	±1°	校准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			.XXX	±0.15										
					单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.					