








☐ SMT AREA
PCB LAYOUT
TOL ±0.05MM

注解

1. 素材要求:

1.1 胶芯: LCP E130i, 防火等级:

UL94V-0. 颜色: 黑色;

1.2 端子: C5191-1/2H, T=0.15MM

1.3 接地片: C2680-H, T=0.20MM

2. 电镀要求:

2.1 端子: 接触区镀金1~30U", 焊接区域镀锡100~120U", 全部区域电镀镍底50~80U".

2.2 接地片: 电镀纯雾锡100U", 全部区域电镀镍底50U".

3. 电气性能要求:

3.1 额定电流 1.0A. 额定电压 12V DC

3.2 耐压交流电压最小250VAC.

3.3 绝缘电阻最小1000M 欧姆.

3.4 接触电阻最大50 毫欧.

4. 环境性能要求:

4.1 使用环境-25摄氏度~80摄氏度

4.2 部件耐热焊接温度符合230摄氏度30~60秒, 260摄氏度10秒要求.

5. 耐久寿命: 5000次MIN.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 3P 6.5H侧压电池座 无柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW03-BB3P2565	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606171523	
			SHEET NO. 1 OF 1	