




1. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. 额定电压(Rated voltage):250V DC/AC.
3. 额定电流(Rated current):3.0A.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Dielectricwithstanding voltage):800V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
7. 适用线规(Apply to gauge):AWG#22~#28.

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE			制图 DRAWING	ROSE			料号 PART NO.	ZX-PHD2.0-2-DZ		版本 REV.	A					
						X.	±0.5	±1'		审核 CHECK	LEO			品名 TITLE	PA2.0(PHD)-WTB公共端子		页次 SHEET	1/1				
											X.X	±0.2	X.XX	±0.1	核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
																单位 UNITS	MM	比例 SCALE	1:1			
1	端子	Phosphor Bronze Bright tin plated											兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.									