







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC
(使用AWG#28~#32, O.D 0.6mm MAX).
7. 耐电压: AC 200V/1分钟.

材质:

1. LCP 本色

Part No	CKT	A	B	C	D
ZX-0.8-2PJK-XM2	2	0.80	1.80	2.30	4.30
ZX-0.8-3PJK-XM2	3	1.60	2.60	3.10	5.10
ZX-0.8-4PJK-XM2	4	2.40	3.40	3.90	5.90
ZX-0.8-5PJK-XM2	5	3.20	4.20	4.70	6.70
ZX-0.8-6PJK-XM2	6	4.00	5.00	5.50	7.50
ZX-0.8-7PJK-XM2	7	4.80	5.80	6.30	8.30
ZX-0.8-8PJK-XM2	8	5.60	6.60	7.10	9.10
ZX-0.8-9PJK-XM2	9	6.40	7.40	7.90	9.90
ZX-0.8-10PJK-XM2	10	7.20	8.20	8.70	10.70
ZX-0.8-11PJK-XM2	11	8.00	9.00	9.50	11.50
ZX-0.8-12PJK-XM2	12	8.80	9.80	10.30	12.30
ZX-0.8-13PJK-XM2	13	9.60	10.60	11.10	13.10
ZX-0.8-14PJK-XM2	14	10.40	11.40	11.90	13.90
ZX-0.8-15PJK-XM2	15	11.20	12.20	12.70	14.70
ZX-0.8-16PJK-XM2	16	12.00	13.00	13.50	15.50
ZX-0.8-17PJK-XM2	17	12.80	13.80	14.30	16.30
ZX-0.8-18PJK-XM2	18	13.60	14.60	15.10	17.10
ZX-0.8-19PJK-XM2	19	14.40	15.40	15.90	17.90
ZX-0.8-20PJK-XM2	20	15.20	16.20	16.70	18.70
ZX-0.8-21PJK-XM2	21	16.00	17.00	17.50	19.50
ZX-0.8-22PJK-XM2	22	16.80	17.80	18.30	20.30
ZX-0.8-23PJK-XM2	23	17.60	18.60	19.10	21.10
ZX-0.8-24PJK-XM2	24	18.40	19.40	19.90	21.90
ZX-0.8-25PJK-XM2	25	19.20	20.20	20.70	22.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE			制图 DRAWING	料号 PART NO.		版本 REV.	A
			X.	± 0.5	$\pm 1^{\circ}$		品名 TITLE	ZX-0.8-NPJK-XM2	页次 SHEET	1/1
			X.X	± 0.2		审核 CHECK	客户料号 CUTM.NO.			
			X.XX	± 0.1		核准 APPROVAL				
						单位 UNITS	MM	比例 SCALE	1:1	
									兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	