


| REVISIONS |                  |          |               |            |        |
|-----------|------------------|----------|---------------|------------|--------|
| REV.      | ECN NO.          | LOCATION | DESCRIPTION   | DATE       | DESIGN |
| A1        | N/A              |          | 图面升级整理图面      | 2025.06.16 | 阿树     |
| A2        | ECN-P-2026040101 | A2 X1    | 产品外观, 尺寸及材质变更 | 2026.04.01 | 阿树     |



- Specifications (规格):
- 1.Voltage rating (额定电压):DC 12V
  - 2.Current rating (额定电流):0.5A AC/DC
  - 3.Withstanding voltage (耐压值):≥100V AC/minute
  - 4.Insulation resistance (绝缘电阻):≥100MΩ Min
  - 5.Contact resistance (接触电阻):≤20mΩ Max
  - 6.Mating cycles (使用寿命): 10,000 cycles Min
  - 7.Operating Force (操作力度):200±100gf
  - 8.Temperature range (使用温度):-10℃~+60℃

| PAPT NO       | L       | foot |
|---------------|---------|------|
| SK-3245S-L1-X | L1:2.00 | A B  |
| SK-3245S-L2-X | L2:2.50 | A B  |
| SK-3245S-L3-X | L3:3.00 | A B  |
| SK-3245S-L4-X | L4:4.00 | A B  |

|      |                |     |                 |                  |
|------|----------------|-----|-----------------|------------------|
| D    | Cover          | 1   | Sus             | Natural          |
| C    | Contact spring | 1   | Phosphor branze | Ag Plated        |
| B    | Keystake       | 1   | PPA/LCP         | Black            |
| A    | Pedestal       | 1   | PPA/LCP(Brass)  | Ag Plated(Black) |
| ITEM | PAPT NAME      | QTY | MATERIAL        | FINISHING(COLOR) |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERAUCES |       |



|          |    |             |                          |
|----------|----|-------------|--------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE: SLIDE SWITCH |
| CHECKED  |    | UNIT: mm/in | PART NO.: SK-3245S-L1-A  |
| APPROVED |    | SIZE: A4    | DWG NO.:                 |

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A2       |

