





SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



2~3P结构样式

4P 结构样式

技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 工作温度: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: 250V DC/AC(rms).
4. 额定电流: 3.0A AC, DC.
5. 接触电阻: $\leq 20\text{m}\Omega$.
6. 耐压值: 800V AC/minute.
7. 绝缘电阻: $\geq 1000\text{M}\Omega$.

Part No	Pin	A	B	C
BX-PHB2.0-2-2PZZ	2*2	2.0	6.0	3.2
BX-PHB2.0-2-3PZZ	2*3	4.0	8.0	3.2
BX-PHB2.0-2-4PZZ	2*4	6.0	10.0	3.0
BX-PHB2.0-2-5PZZ	2*5	8.0	12.0	5.0
BX-PHB2.0-2-6PZZ	2*6	10.0	14.0	7.0
BX-PHB2.0-2-7PZZ	2*7	12.0	16.0	9.0
BX-PHB2.0-2-8PZZ	2*8	14.0	18.0	11.0
BX-PHB2.0-2-9PZZ	2*9	16.0	20.0	13.0
BX-PHB2.0-2-10PZZ	2*10	18.0	22.0	15.0
BX-PHB2.0-2-11PZZ	2*11	20.0	24.0	17.0
BX-PHB2.0-2-12PZZ	2*12	22.0	26.0	19.0
BX-PHB2.0-2-13PZZ	2*13	24.0	28.0	21.0
BX-PHB2.0-2-14PZZ	2*14	26.0	30.0	23.0
BX-PHB2.0-2-15PZZ	2*15	28.0	32.0	25.0
BX-PHB2.0-2-16PZZ	2*16	30.0	34.0	27.0
BX-PHB2.0-2-17PZZ	2*17	32.0	36.0	29.0
BX-PHB2.0-2-18PZZ	2*18	34.0	38.0	31.0
BX-PHB2.0-2-19PZZ	2*19	36.0	40.0	33.0
BX-PHB2.0-2-20PZZ	2*20	38.0	42.0	35.0
BX-PHB2.0-2-21PZZ	2*21	40.0	44.0	37.0
BX-PHB2.0-2-22PZZ	2*22	42.0	46.0	39.0

序号	品名	材质
1	2.0A型双排立式WTB胶芯	PA46 UL94V-0 白色
2	2.0F型卧式2代WTB端子	铜合金/表面镀锡

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PHB2.0-2-NPZZ	版本 REV.	A
			.X	± 0.20	$\pm 2^{\circ}$	审核 CHECK	EVA	品名 TITLE	2.00 Pitch A型双排直插WTB	页次 SHEET	1/1
			.XX	± 0.10		核准 APPROVAL	JADE	客户料号 CUTM.NO.		 Bossie (博锡)	
			.XXX	± 0.05		单位 UNITS	MM	比例 SCALE	1:1		