







1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ 。
3. 额定电压： 30V , AC/DC。
4. 耐电压： 200V , AC/minute。
5. 接触电阻： $\leq 0.02\Omega$ 。
6. 绝缘电阻： $\geq 100\text{M}\Omega$ 。
7. 额定电流： 0.5A AC/DC。



序号	品名	材质
1	0.8-C型卧式WTB胶芯	LCP UL94 V-0 自然色
2	0.8-C型立式WTB端子	铜合金/表面镀锡
3	0.8-C型卧式WTB焊片	铜合金/表面镀锡
4	0.8-C型立式WTB吸盖	LCP UL94 V-0 黑色

Part No	CKT	A	B
ZX-0.8-2PLT-XM2	2	0.80	3.80
ZX-0.8-3PLT-XM2	3	1.60	4.60
ZX-0.8-4PLT-XM2	4	2.40	5.40
ZX-0.8-5PLT-XM2	5	3.20	6.20
ZX-0.8-6PLT-XM2	6	4.00	7.00
ZX-0.8-7PLT-XM2	7	4.80	7.80
ZX-0.8-8PLT-XM2	8	5.60	8.60
ZX-0.8-9PLT-XM2	9	6.40	9.40
ZX-0.8-10PLT-XM2	10	7.20	10.20
ZX-0.8-11PLT-XM2	11	8.00	11.00
ZX-0.8-12PLT-XM2	12	8.80	11.80
ZX-0.8-13PLT-XM2	13	9.60	12.60
ZX-0.8-14PLT-XM2	14	10.40	13.40
ZX-0.8-15PLT-XM2	15	11.20	14.20

Part No	CKT	A	B
ZX-0.8-16PLT-XM2	16	12.00	15.00
ZX-0.8-17PLT-XM2	17	12.80	15.80
ZX-0.8-18PLT-XM2	18	13.60	16.60
ZX-0.8-19PLT-XM2	19	14.40	17.40
ZX-0.8-20PLT-XM2	20	15.20	18.20
ZX-0.8-21PLT-XM2	21	16.00	19.00
ZX-0.8-22PLT-XM2	22	16.80	19.80
ZX-0.8-23PLT-XM2	23	17.60	20.60
ZX-0.8-24PLT-XM2	24	18.40	21.40
ZX-0.8-25PLT-XM2	25	19.20	22.20
ZX-0.8-26PLT-XM2	26	20.00	23.00
ZX-0.8-27PLT-XM2	27	20.80	23.80
ZX-0.8-28PLT-XM2	28	21.60	24.60



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-0.8-NPLT-XM2	版本 REV.	A	
			X.	±0.5	±1°	审核 CHECK	LEO			品名 TITLE	0.80 Pitch C型立式WTB	页次 SHEET	1/1
			X.X	±0.2		核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX	±0.1									
						单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			