






Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC.
3. Rated current: 3.0A DC/AC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage: 800V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge: AWG#24~#28.

序号	品名	材质	制图	变更内容	日期	GENERAL TOLERANCE		制图	EMMA	料号	BX-PHB2.0-2-DZ	版本	A
			DRAWN	DESCRIPTION	DATE	.X	± 0.30	X.*	$\pm 5^{\circ}$	PART NO.		REV.	
1	端子	Phosphor Bronze Bright tin plated				.XX	± 0.25	X.X*	$\pm 1^{\circ}$	审核	EVA	页次	1/1
						.XXX	± 0.15			CHECK		SHEET	
										批准			
										APPROVAL	JADE		
						单位	MM	比例	SCALE	1:1	Bossie (博锡)		