



Technical Index

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 150V DC/AC.
3. Rated current: 1.0A.
4. Contact resistance:
 $\leq 20\text{m}\Omega$ (Initial) per contact,
 $\leq 40\text{m}\Omega$ Change allowed.
5. Dielectric withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 500\text{M}\Omega$.
7. Apply to gauge: AWG#26~AWG#30. (O.D 1.0mm Max)

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-DF1.25-2-DZ	版本 REV.	A
						.X ±0.30	X.* ±5°		审核 CHECK	LEO			品名 TITLE	1.25 Pitch A型(DF13) 双排公头端子 <th>页次 SHEET</th> <td>1/1</td>	页次 SHEET
1	端子	Phosphor Bronze Bright tin plated				.XX ±0.25	X.X* ±1°	核准 APPROVAL		JOHN			客户料号 CUTM.NO.		
						.XXX ±0.15			单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		