








技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V DC/AC.
- 3.额定电流(Rated current):3.0A.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#22~#28.

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-PHD2.0-2-DZ	版本 REV.	A
						X. ± 0.5 $\pm 1^{\circ}$	审核 CHECK	EVA	品名 TITLE	PA2.0(PHD)-WTB公头端子	页次 SHEET	1/1
1	端子	Phosphor Bronze Bright tin plated				X.X ± 0.2	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
						X.XX ± 0.1	单位 UNITS	MM	比例 SCALE	1:1		