








技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):30V AC/DC.
- 3.额定电流(Rated current):0.5A AC/DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectric withstanding voltage):200V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#28~#32(0.06mm MAX).

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-0.8-DZ-XM2		版本 REV.	A
						X.	±0.5 ±1°					品名 TITLE	0.80 Pitch C型WTB公头端子		页次 SHEET	
1	端子	Phosphor Bronze Bright tin plated				X.X	±0.2	审核 CHECK	EVA			客户料号 CUTM.NO.				
						X.XX	±0.1	批准 APPROVAL	JADE			 Bossie (博锡)				
								单位 UNITS	MM	比例 SCALE	1:1					
			1	2	3	4	5	6	7	8	9					