






技术指标:

- 1.温度范围: -25°C~+85°C.
- 2.额定电压: 250V AC,DC.
- 3.耐电压: 800V AC/minute.
- 4.接触电阻: ≤20mΩ .
- 5.绝缘电阻: ≥1000MΩ.
- 6.额定电流: 3A AC,DC.

材料:

1.塑胶: PA66 白色

型号	CKT	A	B
ZX-PHD2.0-2-2PJK	2*2	2.00	6.00
ZX-PHD2.0-2-3PJK	2*3	4.00	8.00
ZX-PHD2.0-2-4PJK	2*4	6.00	10.00
ZX-PHD2.0-2-5PJK	2*5	8.00	12.00
ZX-PHD2.0-2-6PJK	2*6	10.00	14.00
ZX-PHD2.0-2-7PJK	2*7	12.00	16.00
ZX-PHD2.0-2-8PJK	2*8	14.00	18.00
ZX-PHD2.0-2-9PJK	2*9	16.00	20.00
ZX-PHD2.0-2-10PJK	2*10	18.00	22.00
ZX-PHD2.0-2-11PJK	2*11	20.00	24.00
ZX-PHD2.0-2-12PJK	2*12	22.00	26.00
ZX-PHD2.0-2-13PJK	2*13	24.00	28.00
ZX-PHD2.0-2-14PJK	2*14	26.00	30.00
ZX-PHD2.0-2-15PJK	2*15	28.00	32.00
ZX-PHD2.0-2-16PJK	2*16	30.00	34.00
ZX-PHD2.0-2-17PJK	2*17	32.00	36.00
ZX-PHD2.0-2-18PJK	2*18	34.00	38.00
ZX-PHD2.0-2-19PJK	2*19	36.00	40.00
ZX-PHD2.0-2-20PJK	2*20	38.00	42.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-PHD2.0-2-NPJK	版本 REV.	A
			.X ±0.30	X.* ±5°					品名 TITLE	PHD2.0公头胶壳	页次 SHEET	1/1
			.XX ±0.25	X.X* ±1°					客户料号 CUTM.NO.			
			.XXX ±0.15						兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			
					审核 CHECK	LEO						
					核准 APPROVAL	JOHN						
					单位 UNITS	MM	比例 SCALE	1:1				