









REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):

1. 塑件材质: LCP UL94V-0
2. 端子材质: 磷青铜 表面镀锡
3. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
4. 额定电压(Rated voltage): 50V, AC/DC(=等效).
5. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
6. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐压: 200V/1 Minute.



序号 (NO.)	零件名称 (Part. Name)	材质 (Material)
①	0.5 掀盖胶芯 (H=2.0) 0.5 Pitch Easy-on Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	0.5 掀盖端子 (H=2.0) 0.5 Pitch Easy-on Type Terminal (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	0.5 掀盖后盖 (H=2.0) 0.5 Pitch Easy-on Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	0.5 掀盖焊片 (H=2.0) 0.5 Pitch Easy-on Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CUSTOMER DRAWING

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING

CHECKED

APPROVED

TITLE

FPC连接器0.5间距30PIN翻盖下接H2.0 卧贴

REV.

A

TOLERANCES ARE

30-150

±0.35

10-30

±0.2

5-10

±0.15

0-5

±0.1

ANGLE

±3°

PART NO.

LAIL-FPC-CX01-30P0.5-W

UNITS

mm

DWG. NO.

Projection

