




REV.	ECN NO.	DESCRIPTION	DRAW	DATE



NOTE:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.
CONTACTS: COPPER ALLOY.
PEG: COPPER ALLOY.
ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).
- RATING:
OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: -55°C~+85°C.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: -10°C~+50°C.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
INSULATION RESISTANCE >500MΩ.
WITHSTAND VOLTAGE: 200V/1 MINUTE.



CUSTOMER DRAWING		 深圳市莱联电子有限公司 SHENZHEN LAILAN ELECTRONICS CO., LTD			
DRAWING					
CHECKED					
APPROVED					
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-130	±0.2				
5-10	±0.15				
0-5	±0.1	±3°			
		TITLE	FPC连接器0.5间距5PIN翻盖式双侧触点上下载	REV.	A
		PART NO.	LAIL-FPC-CDX01-5P0.5-GW	UNITS	mm
		DWG. NO.		Projection	