






ROHS




31PIN



SECTION
SCALE 2:1



APPLICABLE FFC/FPC
FFC/FPC THICKNESS=0.20±0.03



FFC/FPC INSERT DIRECTION
RECOMMEND PCB LAYOUT

NOTES:

1. MATERIAL:

HOUSING: HIGHT-TEMP PLASTIC,UL 94V-0,COLOR:NATURE;
COVER: HIGHT-TEMP PLASTIC,UL 94V-0,COLOR:BLACK;
TERMINAL: COPPER ALLOY;
PEG: COPPER ALLOY;

2. PLATING:

TERMINAL: GOLD PLATED ON NICKEL OVERALL.
PEG: TIN PLATED ON NICKEL OVERALL.

3. RATING:

CURRENT RATING: 0.3A AC/DC
VOLTAGE RATING: 30V AC/DC
TEMPERATURE RANGE: -55°C~+85°C;
Insulation resistance: ≥500MΩ.
Withstand voltage: 200V/1 minute.

CUSTOMER DRAWING

DRAWING
CHECKED
APPROVED

TOLERANCES ARE

30-150	±0.35	ANGLE ±3°
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO.,LTD

TITLE FPC连接器0.3间距31PIN翻盖下接 卧贴 REV. A

PART NO. LAIL-FPC-CX01-31P0.3-GW UNITS mm

DWG. NO. Projection