


REV.	ECN NO.	DESCRIPTION	DRAW	DATE



24PIN

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$.




OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C} \sim +50^{\circ}\text{C}$.



STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE $\geq 500\text{M}\Omega$.

WITHSTAND VOLTAGE: 200V/1 MINUTE.



SECTION A-A



CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED		TITLE		REV.	A
APPROVED		PART NO.		UNITS	mm
TOLERANCES ARE		DWG. NO.		Projection	
30-150	± 0.35	ANGLE	$\pm 3^{\circ}$		
10-30	± 0.2				
5-10	± 0.15				
0-5	± 0.1				