






REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):


- 1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects, cracks and other phenomena.)
- 2.温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 3.额定电压(Rated voltage): 50V, AC/DC(=等效).
- 4.接触电阻(Contact resistance): $\leq 0.03\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 6.耐压: 200V/1 Minute.





8PIN



SECTION A-A



适用扁平线(Applicable Flat Cable)



序号 (NO.)	零件名称 (Part. Name)	材质 (Material)
①	1.0掀盖胶芯(H=2.0) 1.0 Pitch Easy-on Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	1.0掀盖端子(H=2.0) 1.0 Pitch Easy-on Type Terminal (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	1.0掀盖后盖(H=2.0) 1.0 Pitch Easy-on Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	1.0掀盖焊片(H=2.0) 1.0 Pitch Easy-on Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CUSTOMER DRAWING

LAILAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING

CHECKED

APPROVED

TOLERANCES ARE

30-150

±0.35

10-30

±0.2

5-10

±0.15

0-5

±0.1

ANGLE

±3°

TITLE

FPC连接器1.0间距8PIN翻盖下接H2.0 卧贴

PART NO.

LAIL-FPC-CX01-8P1.0-W

DWG. NO.

UNITS

mm

Projection

