

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Electrical:

Current Rating:1.5Amp max @25°C

Voltage Rating:150VAC max

Insulation Resistance:500 megohms min

Contact Resistance:20 milliohms max(Initial)

Withstanding Voltage:1000 VAC

Mechanical:

Durability:750 Cycles

Operating Temperature:-40°C~+70°C

Storage Temperature:-50°C~+75°C

Contact Normal Force:100g Minimum

Material:

Housing: Thermoplastic UL94V-0,PBT








Shield:0.15mm Thickness Stainless Steel SUS304-1/2H Plated Ni

Contact:0.45mm Dia Phosphor Bronze

Plated Gold Over Ni

For wave Soldering Temperature: 260+/-5°C,5sec/95%Area be covered

Withstand Temperature: 230+/-5°C,5sec No stick tin melting phenomenon



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECKED				
APPROVED				
TOLERANCES ARE		TITLE	RJ45 8P8C带壳带弹左黄右绿	REV. A
30-150	±0.35	PART NO.	LAIL-RJ45-2P-LED4-BY-02-WC	UNITS mm
10-30	±0.2			
5-10	±0.15			
0-5	±0.1	DWG. NO.		Projection