









REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):

- 1.塑件材质: LCP UL94V-0
- 2.端子材质: 磷青铜 表面镀锡
- 3.温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 4.额定电压(Rated voltage): 50V, AC/DC(=等效).
- 5.接触电阻(Contact resistance): $\leq 0.03\Omega$.
- 6.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 7.耐压: 200V/1 Minute.



SECTION A-A



序号 (NO.)	零件名称 (Part Name)	材质 (Material)
①	0.5掀盖胶芯(H=2.0) 0.5 Pitch Easy-on Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	0.5掀盖端子(H=2.0) 0.5 Pitch Easy-on Type Terminal (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	0.5掀盖后盖(H=2.0) 0.5 Pitch Easy-on Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	0.5掀盖焊片(H=2.0) 0.5 Pitch Easy-on Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING		TITLE		FPC连接器0.5间距8PIN翻盖下接H2.0 卧贴	REV.	A
CHECKED						
APPROVED						
TOLERANCES ARE						
30-150	±0.35	ANGLE	PART NO.	LAIL-FPC-CX01-8P0.5-W	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG. NO.		Projection	