






REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500M\Omega$.
6. 耐压: 200V/1 Minute.





5PIN



SECTION A-A



适用扁平线(Applicable Flat Cable)



适用线路板(PCB LAYOUT)

序号 (NO.)	零件名称 (Part. Name)	材质 (Material)
①	1.0 掀盖胶芯(H=2.0) 1.0 Pitch Easy-on Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	1.0 掀盖端子(H=2.0) 1.0 Pitch Easy-on Type Terminal (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	1.0 掀盖后盖(H=2.0) 1.0 Pitch Easy-on Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	1.0 掀盖焊片(H=2.0) 1.0 Pitch Easy-on Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CUSTOMER DRAWING

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING

CHECKED

APPROVED

TOLERANCES ARE

30-150

±0.35

10-30

±0.2

5-10

±0.15

0-5

±0.1

ANGLE

±3°

TITLE

FPC连接器1.0间距5PIN翻盖下接H2.0 卧贴

PART NO.

LAIL-FPC-CX01-5P1.0-W

DWG. NO.

REV.

A

UNITS

mm

Projection