


SPECIFICATIONS:





- 1.VOLTAGE/CURRENT RATING: 30V/AC, DC,0.3A;
- 2.WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN/100V DC.;
- 4.CONTACT RESISTANCE: 90m Ω MAX./1mA,20mV AC,1KHz;
- 5.DURABILITY: 30 CYCLES;
- 6.OPERATING TEMPERATURE RANGE: -35° C TO 85° C.

MATERIAL:

- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: PHOSPHOR BRONZE;

PLATING:

- 1.TERMINAL: CONTACT AREA: GOLD 0.05 μ m"MIN.
SMT LEAD: GOLD 0.025 μ m" MIN.
UNDERPLATING: NICKEL 1 μ m" MIN.



PACKING: R:REEL
O:STANDARD SPECIFICATIONS
COLOR:BLACK

P: PLUG

PIN

PLATING: G:GOLD FLASH

HEIGHT:11--1.14H

F:0.40 BTB

LXWCONN BTB CONNECTOR SERIES

PIN NO.	DIM A	DIM B	DIM C
10	3.52	1.60	1.00
20	5.52	3.60	1.00
24	6.32	4.40	1.20
30	7.52	5.60	1.50
34	8.32	6.40	1.50
40	9.52	7.60	3.20
50	11.52	9.60	3.20
60	13.52	11.60	3.20
70	15.52	13.60	3.20
80	17.52	15.60	3.20
90	19.52	17.60	3.20
100	21.52	19.60	3.20
120	25.52	23.60	3.20

RoHS
Compliant
2013/95/EC



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE
.X ±0.3
.XX ±0.20
.XXX ±0.10
ANGLES ±1°

连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
制图(DR): Johnny 2023.07.03	品名(TITLE): BTB HEADER P0.40
审核(CHKD):	料号(PART NO): LBF**-G**P-BOR01
核准(APPD): Tong 2023.07.03	比例(SCALE): 1:1 单位(UNITS): mm 张数(SHEET): 1 OF 1 图幅(SIZE): A4