

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: $-55^{\circ}\text{C}\sim+85^{\circ}\text{C}$.


OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C}\sim+50^{\circ}\text{C}$.






STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE $\geq 500\text{M}\Omega$.

WITHSTAND VOLTAGE: 200V/1 MINUTE.



10PIN



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED		TITLE	
APPROVED		FPC连接器0.5间距10PIN翻盖式双侧触点上下接	
TOLERANCES ARE		REV.	
30-150	± 0.35	PART NO.	
10-30	± 0.2	LAIL-FPC-CDX01-10P0.5-GW	
5-10	± 0.15	UNITS	
0-5	± 0.1	DWG. NO.	
ANGLE		Projection	
$\pm 3^{\circ}$		mm	