







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- NOTES:
- ELECTRICAL:
- 1. VOLTAGE RATING: 125V AC.
 - 2. CURRENT RATING: 1.5A.
 - 3. CONTACT RESISTANCE: 30 mΩ MAX.
 - 4. INSULATION RESISTANCE: 500 MΩ MIN @ 500V DC.
 - 5. DIELECTRIC STRENGTH: 1000V AC 50Hz or 60Hz,1MIN.
- MECHANICAL:
- 1. INSERT MATERIAL: UL94V-0.
 - 2. CONTACT MATERIAL: $\varnothing 0.46\text{mm}$ C51000(QSn4-0.3)PHOSPHOR BRONZE GOLD PLATING OVER NICKEL.
 - 3. MATING/UNMATING FORCE: 2.2KG.F MAX.
 - 4. RETENTION STRENGTH: 5.0KG.F MIN BETWEEN JACK AND PLUG.
 - 5. OPERATING LIFE: 750 CYCLES MIN.
- ENVIRONMENTAL:
- 1. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ RELATIVE HUMIDITY<70%.
 - 2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



PCB Layout

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD		
CHECKED				
APPROVED				
TOLERANCES ARE		TITLE	RJ45 8P8C直立式无铁壳无灯	REV. A
30-150	±0.35	PART NO.	LAIL-RJ45-LED0-BN-01-ZC	UNITS mm
10-30	±0.2			
5-10	±0.15			
0-5	±0.1	DWG. NO.		Projection