







ROHS



NOTE:

1. MATERIAL:

- 1.1 HOUSING: PBT L94V-0 BLACK
- 1.2 CONTACT: $\phi 0.46$ mm COPPER ALLOY
- 1.3 SHELL: T=0.2mm, COPPER ALLOY

2. FINISH:


- 2.1 CONTACT: G/F PLATED OVER Ni
- 2.2 SHELL: PLATING Ni OVERALL

3. ELECTRICAL:

- 3.1 CONTACT CURRENT RATING: 1.5A MIN.
- 3.2 VOLTAGE RATING :125V AC (rms)
- 3.3 WITHSTANDING VOLTAGE: 1000 VAC
- 3.4 INSULATION RESISTANCE: 500 MEGAOHMS MIN.
- 3.5 CONTACT RESISTANCE: 30 MILLIOHMS MAX.

4. ENVIRONMENTAL :

- 4.1 OPERATING TEMPERATURE: -40°C TO $+85^{\circ}\text{C}$
- 4.2 STORAGE TEMPERATURE: -40°C TO $+85^{\circ}\text{C}$



CUSTOMER DRAWING		WLAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING		TITLE		REV.	A
CHECKED		PART NO.		UNITS	mm
APPROVED		DWG. NO.		Projection	
TOLERANCES ARE					
30-150	± 0.35	ANGLE			
10-30	± 0.2				
5-10	± 0.15				
0-5	± 0.1				