






SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20MΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PBT
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 200° C for 30-60 seconds
(220° C for 5 seconds)



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

Contacts Per ROW	
6pin	28pin
8pin	30pin
10pin	34pin
12pin	36pin
14pin	40pin
16pin	44pin
18pin	50pin
20pin	60pin
24pin	64pin
26pin	

深圳市金航标电子有限公司				www.kinghelm.com			
KH-2.54DC2-2X13P-H17				0755-28190160			
UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: 2.54DC2-NPin H17 180度 PC3.8 PBT 长耳扣					
X : ±0.30	X° : ±5°	SIZE	A4	SCALE	N:1	PROUCT NO.	
X.X : ±0.25	X.X° : ±1°	REV	A	UNIT	mm	PROJECT	
X.XX : ±0.20	X.XX° : ±0.5°						
CHECKED:	陈超凡	2024/08/27	CHECKED:		/ /	APPROVED:	/ /