






SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20MΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PBT
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 200° C for 30-60 seconds
(220° C for 5 seconds)



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

Contacts Per ROW	
6pin	28pin
8pin	30pin
10pin	34pin
12pin	36pin
14pin	40pin
16pin	44pin
18pin	50pin
20pin	60pin
24pin	64pin
26pin	

深圳市金航标电子有限公司

www.kinghelm.com

KH-2.54DC2-2X11P-H17

0755-28190160

UNLESS OTHERWISE SPECIFIED TOLERANCE

X	: ± 0.30	X°	: ± 5°
X.X	: ± 0.25	X.X°	: ± 1°
X.XX	: ± 0.20	X.XX°	: ± 0.5°

DRAWN NAME:

2.54DC2-NPin H17 180度 PC3.8 PBT 长耳扣

SIZE	A4	SCALE	N:1	PROUCT NO.	
REV	A	UNIT	mm	PROJECT	

CHECKED: 陈超凡 2024/08/27 CHECKED: / / APPROVED: / /

G
F
E
D
C
B
A