






- 1.1 Voltage Rating: 60V AC/DC
- 1.2 Rated current : For signal pin 0.3 AMPS/Pin
For power pin 5 AMPS / Pin
- 1.3 Temperature Range: -40 °C to +85°C
- 1.4 Contact Resistance:
Signalpin:Initial:50mΩ MAX
AFTER TEST:Δ20mΩ
Power pin:Initial:15mΩ MAX
AFTER TEST:15mΩ MAX
- 1.5 Insulation Resistance
Initial: 500 MΩ Minimum.
After test: 500 MΩ Minimum.
- 1.6 Dielectric Withstanding Voltage
NO EVIDENCE OF BREAKDOWN IN AC 100 V,
1 MINUTE
- 1.7 MATING-UNMATING FORCE:
MATING FORCE: 1 CYCLE: 40N MAX
30 CYCLE:40N MAX
UNMATING FORCE:1 CYCLE: 10N MIN
30 CYCLE:8N MIN
- 1.8 SALT WATER SPRAY: TEMPERATURE 35°C±2°C
DENSITY OF SALT WATER 5±1%
DURATION:48±2 HOUR
Storage Temperature Range -40°C to +85°C
0 to 90 % RH (Relative humidity).




3	POWER CONTACT	COPPER ALLOY, Au3u" Min ON CONTACT AREA, Au1u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER			6	REEL	PLASTIC
2	SIGNAL CONTACT	COPPER ALLOY, Au3u" Min ON CONTACT AREA, Au1u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER			5	COVER TAPE	PLYESTER
1	HOUSING	LCP ,BLACK, UL 94 V-0			4	EMBOSSED CARRIER TAPE	PS
NO.	PART NAME	DESCRIPTION , REMARKS			NO.	PART NAME	DESCRIPTION , REMARKS
GENERAL	TOLERANCE	UNITS:mm	SCALE 1 : 1		TITLE: BTB CONN, Plug, MHO. 6, P0. 30mm, 78pin		
X. ± 0.30	X.* ± 5"	APPROVED	LEO		DRAWING NO. : C-BB0026P-01		X
.XX ± 0.20	.X* ± 3"	CHECKED	Gong		PART NO. : KH- BB0026P78A		
.XX ± 0.15	.XX* ± 2"	DESIGNED	Qiang		1		

Kinghelm®




DIRECTION OF UNREELING



TRAILER

TAPING (FREE)

LEADER



STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS

Rohs 2.0
Compliant



HF

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

NO.				PART NAME				DESCRIPTION , REMARKS			
GENERAL	TOLERANCE	UNITS:mm	SCALE 1 : 1	TITLE: BTB CONN, Plug, MHO. 6, P0. 35mm, 78Pin				DRAWING NO. : C-BB0026P-1			
X. ± 0.30	X.* ± 5°	APPROVED	LEO	PART NO. : KH-BB0026P78A				X3			
.X ± 0.20	.X* ± 3°	CHECKED	Tom					2			
.XX ± 0.15	.XX* ± 2°	DESIGNED	GONG					2			