


印制线路板 (PCB Layout)



技术参数

SPECIFICATIONS

间距(Pitch) : 1.0

极数(Poles) :3~40

额定电压(Voltage rating):50V DC/AC

额定电流(Current rating) :0.5A DC/AC

耐压值(Withstand Voltage) :500V AC/m

工作温度(Working Temperature) : -25℃~+85℃

绝缘电阻(Insulation Resistance) : ≥500MΩ



接触电阻(Contact resistance) : ≤30MΩ

单面接触(Single contact)

材料Material

接触件(Contact) : 磷青铜镀银锡 Phosphor Bronze Tin-plated

塑胶主体 (Housing) : 耐热树脂 (UL94V-0) Heat resistance plastic (UL94V-0)



芯数	A	B	C
03	6.05	4.10	2.00
04	7.05	5.10	3.00
05	8.05	6.10	4.00
06	9.05	7.10	5.00
07	10.05	8.10	6.00
08	11.05	9.10	7.00
09	12.05	10.10	8.00
10	13.05	11.10	9.00
11	14.05	12.10	10.00
12	15.05	13.10	11.00
13	16.05	14.10	12.00
14	17.05	15.10	13.00
15	18.05	16.10	14.00
16	19.05	17.10	15.00
17	20.05	18.10	16.00
18	21.05	19.10	17.00
19	22.05	20.10	18.00
20	23.05	21.10	19.00
21	24.05	22.10	20.00
22	25.05	23.10	21.00
23	26.05	24.10	22.00
24	27.05	25.10	23.00
25	28.05	26.10	24.00
26	29.05	27.10	25.00
27	30.05	28.10	26.00
28	31.05	29.10	27.00
29	32.05	30.10	28.00
30	33.05	31.10	29.00
31	34.05	32.10	30.00
32	35.05	33.10	31.00
33	36.05	34.10	32.00
34	37.05	35.10	33.00
35	38.05	36.10	34.00
36	39.05	37.10	35.00
37	40.05	38.10	36.00
38	41.05	39.10	37.00
39	42.05	40.10	38.00
40	43.05	41.10	39.00